





WE ARE PASSIONATE ABOUT WHAT WE DO

We love what we do. You can see that in the quality of our test and measurement systems and in the satisfaction of our customers.

"You are always solution-oriented and always try to help us somehow, even if there is sometimes no technical solution." - Framatome -

"Thank you very much for supporting us in such a way that we can serve our projects, despite the difficulties in procurement, which I can understand. I am very glad that I chose DEWETRON."

- Siemens Amberg -

"With the old software, I had to do a lot of trickery; that's not necessary with OXYGEN. Well thought out from start to finish."

- IABG -


We know that your developments depend on the reliability and accuracy of our measurement systems and therefore they have top priority. We work to the highest quality standards and guarantee you reliable and highly precise measurement data since 1989. We stand for Austrian quality.

The measurable difference.




Scan to download this Product Guide










CONTENTS

PORTFOLIO & SERVICES	4
HIGHEST QUALITY MADE IN AUSTRIA	6
SYSTEM OVERVIEW	7
TRION & TRION3 MODULES	8
ANALOG OUTPUT	10
POWER ANALYSIS	12
TEST STAND INTEGRATION	14
ALL-IN-ONE SYSTEMS	15
MAINFRAME SYSTEMS	16
RACK-MOUNT MAINFRAMES	17
FRONT-ENDS: TRIONet3	18
VERY RUGGED FRONT-END NEX[DAQ]	19
PURE RECORDING PU[REC]	20
MSI SENSOR ADAPTER	21
LOW-SPEED CHANNEL EXPANSIONS	.22
ANALOG SIGNAL CONDITIONING	23
SYNCHRONIZED SYSTEMS	24
OXYGEN MEASUREMENT SOFTWARE	26
SDK FOR PROGRAMMERS	32
LINUX	33
LABVIEW™ INTEGRATION	35
CUSTOMER CARE CENTER	36
ELECTRICAL POWER & NVH	38
ACCECCODIEC	70









PORTFOLIO & SERVICES

RELIABLE and PRECISE measurement data play an essential role in your daily business? The requirements in your CHALLENGING test and measurement tasks change frequently and you need to be very FLEXIBLE? The DAQ hardware and even the used software should be CUSTOMIZABLE and EASY TO USE?

We listen to our customers and offer MODULAR DAQ SOLUTIONS – you have the choice.

CONFIGURE YOUR INDIVIDUAL DAQ SOLUTION

CHASSIS



MODULES




SOFTWARE



DIFFERENT CHASSIS LIKE ALL-IN-ONE WITH DISPLAY, FRONT-END, 19" RACK-MOUNT...




USER-EXCHANGEABLE TRION(3) MODULES FOR ALL INPUT SIGNALS: UP TO 10 MS/S



OXYGEN MEASUREMENT SOFTWARE: POWER ANALYSIS, ORDER ANALYSIS, FFT.

MEASUREMENT CHAIN OF ANALOG SIGNALS

TRION(3) modules are the heart of every DEWETRON measurement system. The sensing of physical parameters such as vibrations, strains, noise, pressure, force, current etc. is usually carried out with sensors that output analog signals. TRION(3) modules take over the precise signal conditioning, digitization and filtering of these signals and make the data available for further processing and storage.



In addition, TRION(3) modules provide strong and stable sensor excitation and various types of industrial connectors, making it easy to connect every sensor!

YOUR DAQ SYSTEM



FOR EXAMPLE: DEWE3-A4, DEWE3-PA8 POWER ANALYZER, DEWE3-A4L, TRIONet3, DEWE3-M4, DEWE3-RM16, DEWE3-PA8-RM

CUSTOMER CARE CENTER



CALIBRATION (ISO 17025)



FIRST LEVEL SUPPORT



SYSTEM UPGRADE



SECOND LEVEL SUPPORT



5-YEAR **WARRANTY EXTENSION**



DEWETRON TRAINING **ACADEMY**



REPAIR





RENTAL SERVICE

PROCESSED SIGNALS IN 100 % SYNC



VOLTAGE



CURRENT



POWER



THERMO-COUPLE













IEPE© (VIBRATION)



BRIDGE



CHARGE

RTD



COUNTER



VIDEO



SOUND



GPS SYNC



IRIG SYNC



PTP SYNC



PPS SYNC



IMU



SENSOR ADAPTER



DIGITAL INPUT



DIGITAL I/O



ANALOG OUTPUT



SCPI

Interface

SCPI



CAN-FD



CAN J1939



Slave XCP



ETHERCAT



FI FXRAY



ARINC-BUS



MII -RUS

HIGHEST QUALITY MADE IN AUSTRIA

Our commitment to Total Quality Management is based on understanding what is important for the success of our customers. It starts with the definition of the technical specification, covers development, production, quality control, shipment and ends with support and service of our systems during operation. All DEWETRON products go through a tough product qualification phase before being approved for the market. With our quality control methods, we can assure you the highest reliability so that the products fulfill their function over a long period of time.



RADIATED IMMUNITY

We test the immunity of our devices against radiated disturbances by using a generator and an antenna to create a strong modulated, electromagnetic field. Testing is conducted in a special anechoic test chamber, in a certified contract lab.



OPERATING & STORING TEMPERATURE, HUMIDITY

We use climate chambers to validate our environmental specifications (e.g. temperature ranges of -40 to +70 °C). So we can ensure, that our DEWETRON products can be used on a Swedish ice lake as well as in Nevada's desert.




ESD IMMUNITY (ELECTROSTATIC DISCHARGE)

If an electrostatically charged object touches a conductive part of a device, an unwanted, sudden flow of electricity is induced, which can destroy electrical circuits. We simulate this with our ESD (electrostatic discharge) gun.



THERMAL TESTING

We use thermal testing to detect any potential hotspot, component failures during operation, or other issues that could lead to unexpected performance.



MECHANICAL & SEISMIC SHOCK, VIBRATION

We test all of our devices on electrodynamic shakers to simulate vibrations and impacts during operation and transport.



BURST/SURGE IMMUNITY, VOLTAGE DIPS

We simulate voltage dips, power interruptions, surge and burst phenomena during our product qualification tests using special generators.

SYSTEM OVERVIEW





ALL-IN-ONE

SYSTEMS



POWER ANALYZER

- > Up to 16 power phases
- > 0.03 % measurement error (1 to 1000 Hz)
- > Additional, mixed signals
- > Integrated redundant current transducer supply

Consisting of these parts:









- > Built-in display
- > Compact and flexible configuration
- > Powerful PC inside for fast online displays and analysis
- > Battery power option

Consisting of these parts:









MAINFRAME SYSTEMS

- > Powerful PC inside for fast online displays and analysis
- > Can be used with external monitor
- > The ideal solution for installations in a 19" rack

Consisting of these parts:













FRONT-END SYSTEMS

- > Used with an external computer
- > Ideal for small channel count application
- > Fully synchronized expansion for all-in-one or mainframes
- > Multiple units can be daisy-chained
- > Connected via USB3.0 or GBit-Ethernet

Consisting of these parts:



LEGEND:



DATA LOGGER PU[REC]

- > Powerful data logger
- > 16 measurement channels
- > Channel count expandable via
 - > XR modules or
 - > MSI sensor interfaces

Consisting of these parts:





SIGNAL CONDITIONING

- > Stand-alone analog signal conditioning
- > Front-ends for existing recorders, A/D boards ...
- > Up to 300 kHz bandwidth

Consisting of these parts:





Signal conditioning amplifiers





Built-in computer



Display



TRION & TRION3 **MODULES**

Choose from our various TRION(3) signal conditioning modules to measure analog signals from any sensor absolute synchronously. Enjoy maximum flexibility with these user-exchangeable modules featuring A/D conversion on each channel and anti-aliasing filters.

ANALOG MODULES		CHANNELS	PER CHANNEL	RESOLUTION	ISOLATION	CONNECTOR TYPES
TRION3 -1850-MULTI ¹⁾ TRION3 -1820-MULTI ¹⁾ TRION-1820-MULTI		4 or 8	1850: 5 MS/s 1820: 2 MS/s	24-bit >2MS/s: 18-bit	yes	4 D-SUB or 8 LEMO OB
TRION-2402-MULTI	CAN MSI	4 or 8	200 kS/s	24-bit	yes	4 D-SUB or 8 LEMO 0B
TRION-1620-ACC		6	2 MS/s	24-bit >1 MS/s: 16-bit	yes	6 BNC or LEMO 1B
TRION-1620-LV	V ₁₀₀ I	6	2 MS/s	24-bit >1 MS/s: 16-bit	yes	6 BNC or LEMO 1B
TRION3 -1810-HV ¹⁾	V 1000	4 to 8	1 MS/s	24-bit	yes	Safety banana, CAT III 1000 V ³⁾
TRION-1810-HV	V 1000	4 to 8	1 MS/s	24-bit	yes	Safety banana, CAT III 1000 V ³⁾
TRION3 -1810-SUB-8 1)	V I	8	1 MS/s	20-bit	yes	Safety banana
TRION-1603-LV	V ₁₀₀ I	6	250 kS/s	16-bit	yes	6 BNC or LEMO 1B
TRION-2402-dSTG		8	200 kS/s	24-bit	no	8 LEMO 0B, 8 RJ45
TRION-2402-dACC		6 or 8	200 kS/s	24-bit	no	6 BNC or 8 SMB
TRION3 -1802-dLV 1)	$\begin{array}{ c c c c c c c c c c c c c c c c c c c$	16 or 32	200 kS/s 100 kS/s	18-bit 24-bit	no	D-SUB
	$\begin{array}{ c c c c c c c c c c c c c c c c c c c$	16 or 32	20 kS/s	16-bit	no	D-SUB

DIGITAL MODULES		CHANNELS	SAMPLE RATE PER CHANNEL	RESOLUTION	ISOLATION	FEATURES
TRION-CNT	00 ⁶ 7	6	2 MS/s	80 MHz	yes	6 advanced counter
TRION-DI-48	DI	48	2 MS/s	500 ns	yes	48 high-speed digital IN
TRION-BASE	00 ⁶ 0 IRIG	-	2 MS/s	80 MHz	no	Basic IO card with simple IRIG sync and 2 counter
TRION-VGPS-V3	D C C C C C C C C C C C C C C C C C C C	-	2 MS/s	0.01 km/h <10 cm	no	100 Hz GNSS receiver for automotive applications
TRION-TIMING-V3	D C C C C C C C C C C C C C C C C C C C	-	2 MS/s	12.5 ns	no	Applies precision absolute time to measured data
TRION-CAN	CAN	4	1 MBit	-	yes	D-SUB
TRION-ARINC	ARINC 429	4 or 16	-	-	no	Decoding of ARINC 429 signals, export of decoded signals
TRION-MIL1553	MIL 1553	1 or 4	-	-	no	Decoding of MIL-STD-1553, export of decoded signals
TRION-EtherCAT-1-SLAVE	D I	100	500 S/s	-	no	Measurement data output

POWER MODULES		CHANNELS	SAMPLE RATE PER CHANNEL	RESOLUTION	ISOLATION	CONNECTOR TYPES
TRION3 -1810M-POWER ^{1) 2)}	V I	8 (4 U / 4 I)	10 MS/s	18-bit	yes	Safety banana, exchangeable sub-modules
TRION3 -1820-POWER 1) 2)	V I	8 (4 U / 4 I)	2 MS/s	18-bit	yes	Safety banana, exchangeable sub-modules
TRION-1820-POWER ²⁾	V I I	8 (4 U / 4 I)	2 MS/s	24-bit	yes	Safety banana, exchangeable sub-modules
TRION3 -1810-HV 1) 2)	V 1000	8 (4 U / 4 I)	1 MS/s	24-bit	yes	Safety banana, exchangeable sub-modules
TRION-1810-HV ²⁾	V 1000	8 (4 U / 4 I)	1 MS/s	24-bit	yes	Safety banana, exchangeable sub-modules
TRION3 -1810-SUB-8 1) 2)	V I I	8	1 MS/s	18-bit	yes	Exchangeable sub-modules

¹⁾ All TRION3 modules require a DEWE3 chassis ²⁾ These modules occupy 2 TRION(3) slots

ANALOG OUTPUT MODULES	5	CHANNELS	SAMPLE RATE PER CHANNEL	RESOLUTION	ISOLATION	CONNECTOR TYPES
TRION3 -1850-MULTI-AOUT ^{1) 2)}	$\begin{array}{c c} \bullet & & & & \\ \bullet & & & & \\ \hline \end{array}$	IN: 8 OUT: 8	IN: 5 MS/s OUT: 2.5 MS/s	IN: 24-bit OUT: 16-bit or 32-bit	IN: yes OUT: yes	IN: LEMO OB OUT: D-SUB, BNC
TRION3 -1820-MULTI-AOUT ^{1) 2)}	$\begin{array}{c c} \bullet & & & & \\ \bullet & & & & \\ \hline \end{array}$	IN: 8 OUT: 8	IN: 2 MS/s OUT: 2.5 MS/s	IN: 24-bit OUT: 16-bit or 32-bit	IN: yes OUT: yes	IN: LEMO OB OUT: D-SUB, BNC
TRION3 -AOUT-8 1)	AO	OUT: 8	OUT: 2.5 MS/s	OUT: 16-bit or 32-bit	OUT: yes	OUT: D-SUB, BNC

¹⁾ All TRION3 modules require a DEWE3 chassis ²⁾ These modules occupy 2 TRION(3) slots

MAXIMUM FLEXIBILITY WITH PLUG&PLAY TRION(3) MODULES

You are absolutely flexible with the user-exchangeable TRION(3) modules: Choose your suitable TRION(3) modules, plug them into your DEWE3 DAQ system, turn the system on and get to work. The modules are automatically identified and configured within the software as soon as it is launched.



ANALOG OUTPUT

The TRION3-x-AOUT modules offer several ways to output analog signals for different use cases such as signal conditioning, waveform generation or playback of recorded data. In particular, true 3-way isolation, bandwidth of up to 600 kHz for the analog output and the industry-leading dynamics, which is achieved by 32-bit D/A-converters, must be emphasized.



UNIVERSAL SIGNAL CONDITIONING & PROCESSING **ANALOG INPUT SIGNALS** ISOLATED CONDITIONED OUTPUT SIGNALS VOLTAGE **OUTPUT SIGNALS** $\pm 5 \text{ V} \text{ (e.g. 2 mV/V} \triangleq \pm 5 \text{ V)}$ ±10 V CURRENT 0 - 5 V 0 - 10 V ±30 mA IEPE© 0 - 30 mA (VIBRATION) **REAL-TIME SIGNAL** BRIDGE **PROCESSING** > Actual value > Average RTD > RMS > MATH (A+B, A-B, AxB) POTENTIOMETER **SIGNAL GENERATION** > Constant output > Voltage up to ±10 V COUNTER > Current up to ±30 mA > Stream output > Replay recorded data > Live stream output CAN-BUS > Function generator (sine, square,

TRION3-18XX-MULTI-AOUT-8 MODULES

These universal signal conditioning & processing modules are typically used when it comes to mission-critical applications in which the sensor data must be stored redundantly.

In these cases, after conditioning, digitization and filtering of the analog signals, the data is sent to the DEWE3 system's CPU via the PXIe interface as usual but additionally made available in parallel as analog signals for a second

digitization system. Since the signal processing and the analog output run independently, the measurement data is available to the redundant system at all times, even if there is a problem in the main system.

ADDITIONAL FUNCTIONS

To make things even better, onboard real-time data processing is available, so the analog

output can represent not only the actual input value, but also average or RMS values. Simple calculations such as addition, subtraction or multiplication of channel data are also possible. All channels and values can be freely assigned to the available output connectors. Of course, these modules can also be used for signal generation or to replay recorded data

files, see details at TRION3-AOUT-8.

triangle, custom pattern)

ANALOG OUTPUT MODULES	5	CHANNELS	SAMPLE RATE PER CHANNEL	RESOLUTION	ISOLATION	CONNECTOR TYPES
TRION3 -1850-MULTI-AOUT ^{1) 2)}	$\begin{array}{c c} \blacksquare & \bigcirc & \bigcirc & \bigcirc & \bigcirc & \square & \square \\ \blacksquare & \square & \square & \square & \square & \square & \square \\ \blacksquare & \square \\ \end{array}$	IN: 8 OUT: 8	IN: 5 MS/s OUT: 2.5 MS/s	IN: 24-bit OUT: 16-bit or 32-bit	IN: yes OUT: yes	IN: LEMO OB OUT: D-SUB, BNC
TRION3 -1820-MULTI-AOUT ^{1) 2)}	$\begin{array}{c c} \blacksquare & \bigcirc & \bigcirc & \bigcirc & \bigcirc & \square & \square \\ \blacksquare & \square & \square & \square & \square & \square & \square \\ \blacksquare & \square \\ \end{array}$	IN: 8 OUT: 8	IN: 2 MS/s OUT: 2.5 MS/s	IN: 24-bit OUT: 16-bit or 32-bit	IN: yes OUT: yes	IN: LEMO OB OUT: D-SUB, BNC
TRION3 -AOUT-8 1)	AO	OUT: 8	OUT: 2.5 MS/s	OUT: 16-bit or 32-bit	OUT: yes	OUT: D-SUB, BNC
1) All TRION3 modules require a DEWE3 chassis						


²⁾ These modules occupy 2 TRION(3) slots

POWERFUL SIGNAL GENERATION



SIGNAL GENERATION

- > Constant output
 - > Voltage up to ±10 V
 - > Current up to ±30 mA
- > Stream output
 - > Replay recorded data
 - > Live stream output
- > Function generator (sine, square, triangle, custom pattern)



ARBITRARY WAVEFORM

TRION3-AOUT-8 MODULES

The TRION3-AOUT-8 modules are very powerful signal generation modules. Each module provides 8 isolated output channels for voltage (± 5 V, ± 10 V) or current (± 30 mA) signals. The simplest application is the output of constant signals as default values or for simple control processes.

The FPGA based arbitrary waveform generator not only supports the generation of sine, square or triangle signals but also enables users to load their own custom patterns. The so called "stream output" mode enables the replay of recorded data channels as analog signals during a measurement. This simplifies reference curve generation during a measurement significantly.

DAC MODES

Set the high-speed or high-resolution mode individually for every channel.

DAC MODE	HIGH-SPEED	HIGH- RESOLUTION
UPDATE RATE	2.5 MS/s	500 kS/s
DAC RESOLUTION	16-bit	32-bit
LATENCY	<5 μs	<100 µs
BANDWIDTH	600 kHz	70 kHz

POWER ANALYSIS

Build the power analyzer you need with our dedicated power modules. The perfect power analyzer for every field of application.

- > Modular high-precision tailormade power analyzer
- > Acquisition of additional inputs such as thermocouple, IEPE, counter, CAN, GPS, video, SCPI, etc.
- > Up to 16 power phases $(16 \times U + 16 \times I)$, expandable
- > Redundant, integrated current transducer supply
- > Various test bed integration possiblities
- > Remote configuration and control

EVERY DEWETRON SYSTEM CAN BE A POWER ANALYZER.















HIGH-END POWER ANALYZER





POWER ANALYZER	NALYZER DEWE3-PA8				
Slots for TRION / TRION3 modules	8 TRION / TRION3	(up to 16 phases)			
High-speed channel expansion	Add TRIONet3 o	or OXYGEN-NET			
Low-speed channel expansion	XR mo	odules			
Data storage	1 TB Solid State Disk de	dicated for data storage			
Optional data storage	(SSD-PCle-1T-2T) Upgrade from 1 TB to 2 TB industrial grade, PCle attached Solid State Disk				
Gapless storing rate	Тур. 1	L GB/s			
Display	11.6" multi-touch wide-screen, Full HD	No display			
POWER SUPPLY					
Input voltage (max.)	90 to 2	264 V _{AC}			
Sensor power supply	8 x (±15 V / +9 V)	8 x or 16 x (±15 V / +9 V)			
Integrated current transducer supply	Yes, with redu	undant supply			
DIMENSIONS					
Dimensions (W x D x H) without handle/feet	441 x 435 x 222 mm (5 u) (17.4 x 17.1 x 8.7 in.)	442 x 435 x 222 mm (5 u) (17.4 x 17.1 x 8.7 in.)			
Weight without modules and batteries	Typ. 14 kg (30.9 lb.)	Typ. 15.8 kg (34.8 lb.)			

INDIVIDUAL INPUT CONFIGURATION

We offer you a unique modularity: 4 slots of each power module or even 8 slots of the TRION3-1810-SUB-8 can be equipped with different sub-modules. Choose between direct current measurement modules or voltage modules to connect almost any kind of current or voltage transducer.

Create your individual input configurations with our sub-modules. They are user-exchangeable at any time and automatically detected. The calibration data is directly stored inside the sub-module.









TRION(3)-18xx-POWER

	SUB-MODULE		RANGE	SAFETY	BANDWIDTH	CONNECTOR	USER- EXCHANGEABLE
	1 V module		1 V _{RMS} (±2 V _{PEAK})		5 MHz	D-SUB-9 socket	
	5 V modules		5 V _{RMS}	Not isolated. Depending on connected clamp	5 MHz	D-SUB-9 socket	
Ж	5 v modules		(±10 V _{PEAK})	connected clamp	100 kHz	D-SUB-9 socket	
VOLTAGE	600 V module		600 V _{RMS} (±1500 V _{PEAK})		300 kHz	Safety banana	Yes
	5 V module		5 V _{RMS} (±10 V _{PEAK})	CAT II 600 V, isolated	· ·	Safety banana	0 X 0
	XV module	6 6	$\begin{array}{c} 600 V_{RMS}(\pm 1000 V)^{ 2)} \\ 60 V_{RMS}(\pm 100 V) \\ 6 V_{RMS}(\pm 10 V) \\ 0.6 V_{RMS}(\pm 1 V) \end{array}$		300 kHz	Safety banana	
	20 A module	20 A L	20 A _{RMS} (±40 A _{PEAK})				
CURRENT	2 A module	2 A 6	2 A _{RMS} (±4 A _{PEAK})	CAT II 600 V,	300 kHz	Safety banana	00
S	1 A module		1 A _{RMS} (±2 A _{PEAK})	unfused	unfused 300 kHz	(male)	000
	0.2 A module	0.2 A	0.2 A _{RMS} (±0.4 A _{PEAK})				

¹⁾ Max. allowed input: 600 V CAT II (850 V_{PEAK})

FIXED HIGH-VOLTA	GE INPUTS	RANGE	SAFETY	BANDWIDTH	CONNECTOR	USER- EXCHANGEABLE
Voltage input U1, U2, U3, U4		1000 V _{RMS} (±2000 V _{PEAK})	CAT IV 600 V / CAT III 1000 V	5 MHz	Safety banana	No



DEWETRON offers several solutions for current measurement from simple shunts to current clamps and high-precision zero flux transducers. There are versions for pure AC current which do not need any power supply and versions for DC and AC current which can be supplied from the DEWETRON instrument. Sensors requiring ±15 V or +9 V supply voltage can be powered directly. Therefore, sensors such as zero-flux transducers do not need an extra power supply.



TEST STAND INTEGRATION

Leading test stand manufacturers rely on the measurement data from DEWETRON when it comes to reliable testing of important and critical components. Our various interfaces guarantee you a simple integration.

TEST STAND INTERFACES IN OXYGEN

Smart interface technology makes it easy to integrate DEWETRON power analyzers and measurement instruments into various test stand automation systems, such as PAtools® from Kratzer Automation. Depending on the system architecture of the test stand, DEWETRON systems are equipped with the right interface to ensure reliable data transmission, easy to use remote control and remote configuration, e.g. through TCP/IP-based protocols.

EtherCAT

INTERFACE

Typ. 100 ch Typ. 500 S/s per channel

Data transfer & remote control

CAN

CAN-FD

Typ. 20 ch

Typ. 100 S/s per channel

DATA STREAM
OVER ETHERNET

Typ. >100 ch Up to 2 MS/s per channel

SCPI

OVER ETHERNET

Typ. 100 ch Up to 10 kS/s per channel

Data transfer & advanced remote control

XCP

OVER ETHERNET

Typ. 20 ch Up to 10 kS/s per channel

Interface to CANape and INCA

DMD

READER

Software data exchange library

DEDICATED REAL-TIME POWER ANALYSIS SOLUTION

DEWETRON offers a dedicated solution for latency critical tests and applications to turn your DEWE3 system into a real-time Power Analyzer

- > Calculation of cycle-by-cycle power values
- > Data output interface: Ethernet UDP or EtherCAT Slave
- > Data output rate: 1 kHz
- > Typical I/O latency: 2 ms (max: 4 ms)



2 ms (max. 4 ms)
Typical I/O latency

DATA TRANSFER



ALL-IN-ONE SYSTEMS

- > Compact and flexible configuration
- > Convenient for mobile applications with built-in display
- > Powerful PC inside for fast online displays and analysis









	DEWE3-A4	DEWE3-A4L	DEWE2-A13
Slots for TRION / TRION3 modules	4 TRION / TRION3	4 TRION / TRION3	13 TRION
High-speed channel expansion		Add TRIONet3 or OXYGEN-NET	
Low-speed channel expansion		XR modules	
Data storage	512 G	1 TB SSD dedicated for data storage B SSD for operating system and application so	ftware
Optional data storage		Up to 4 TB SSD	
Gapless storing rate	Typ. 400 MB/s	Typ. 400 MB/s	Typ. 90 MB/s
Display	13" TFT multi-touch, Full HD	15.4" multi-touch wide-screen display, Full HD	17" wide-screen display, Full HD
POWER SUPPLY			
Input voltage (max.)	$10\text{to}~36~\text{V}_\text{DC}$ isolated incl. external AC power supply	90 to 264 V _{AC}	90 to 264 V _{AC}
Option 1	Internal buffer battery for ~5 min operation	-	DC power supply (DW2-PS-DC-300) 10 to 36 V_{DC}
Option 2	(DW2-UPS-250-DC) External battery pack, 3 battery slots for ~2 h operation	-	(DW2-PS-BAT) Battery powered, 4 battery slots for ~2 h operation
DIMENSIONS			
Dimensions (W x D x H) without handle/feet	318 x 253 x 128 mm (12.5 x 10 x 5 in.)	462 x 320 x 135 mm (18.2 x 12.6 x 5.3 in.)	450 x 246 x 303 mm (17.7 x 9.7 x 11.9 in.)
Weight without modules and batteries 1)	Typ. 5.9 kg (13 lb.)	Typ. 8.5 kg (18.7 lb.)	Typ. 15 kg (33 lb.)

OPTIONS AND ACCESSORIES



External battery pack: 250 W UPS with 3 battery slots [DW2-UPS-250-DC]




Connection box to power eight current transducers [DW2-CLAMP-DC-POWER-8]



Industrial USB 3.0 cameras for video input [CAM-ALVIUM-x]

MAINFRAME SYSTEMS

- > Compact and flexible configuration
- > Convenient for mobile applications
- > Powerful PC inside for fast online displays and analysis







	DEWE3-M4	DEWE3-M8s
Slots for TRION / TRION3 modules	4 TRION / TRION3	8 TRION / TRION3
High-speed channel expansion	Add TRIONet3 o	or OXYGEN-NET
Low-speed channel expansion	XR me	odules
Data storage	1 TB SSD dedicated for data storage 512 GB SSD for operating system and application software	1 TB SSD dedicated for data storage 512 GB SSD for operating system and application software
Optional data storage	Up to 4 TB	Up to 4 TB
Gapless storing rate	Typ. 400 MB/s	Тур. 800 МВ/s
POWER SUPPLY		
Input voltage (max.)	10 to 36 V _{pc} isolated; incl. external AC power supply	10 to 36 V _{DC} isolated; incl. external AC power supply; optional battery powered; 2 separate power inputs for mutual power supply backup
Option 1	(DW2-PS-DC-Buffer) Internal buffer battery for ~5 min. operation	n/a
Option 2	(DW2-UPS-250-DC) External battery pack, 3 battery slots	n/a
DIMENSIONS		
Dimensions (W x D x H) without handle/feet	318 x 253 x 108 mm (12.5 x 10 x 4.3 in.)	$339 \times 281 \times 239 \text{ mm (5 u)}$ (13.3 x 11.1 x 9.4 in.)
$\textbf{Weight} \text{ without modules and batteries } ^{1)}$	Typ. 3.9 kg (8.6 lb.)	Typ. 9.1 kg (20.06 lb.)
1) Weight of one battery: 540 g (1.20 lb.)		

OPTIONS AND ACCESSORIES



Box for connecting up to 4 GigE cameras; with integrated power supply [CAM-GIGE-SPLIT-01-BOX]



Optional 10 GBit LAN interface available for DEWE3-A4, DEWE3-M4 and DEWE3-RMx



Box for powering up to 8 current transducers [DW2-CLAMP-DC-POWER-8]

RACK-MOUNT MAINFRAMES

- > Rack-mount or benchtop data acquisition mainframe
- > Silent cooling, easy to maintain fan slot
- > Gapless storage of raw data up to 1 GB/s











	DEWE3-RM4	DEWE3-RM8	DEWE3-RM12	DEWE3-RM16				
	DEWES-RM4	DEWES-KINO	DEWES-KMIZ	DEWES-KMIO				
Slots for TRION / TRION3 modules	4 TRION / TRION3	8 TRION / TRION3	12 TRION / TRION3	16 TRION / TRION3				
High-speed channel expansion		Add TRIONet3 or OXYGEN-NET						
Low-speed channel expansion		XR modules						
Data storage	1 TI	1 TB high-speed PCle Solid State Disk dedicated for data storage (removable) 512 GB SSD for operating system and application software						
Optional data storage	(SSD-PCle-1T-2T) Upgrade from 1 TB to 2 TB industrial grade, PCle attached Solid State Disk							
Gapless storing rate	Typ. 1 GB/s							
POWER SUPPLY								
Input voltage (max.)	90 to 264 V _{AC}							
DIMENSIONS								
Dimensions (W x D x H) without handle/feet	442 x 435 x 222 mm (5 u) (17.4 x 17.1 x 8.7 in.)							
Weight without modules	Typ. 15.8 kg (34.8 lb.)							

FRONT-END OPTION FOR MAINFRAME SYSTEMS

If your measurement system should not or may not have a Windows operating system and no application software running on the system itself, we have the solution. We can turn the mainframe chassis into a front-end system by installing our special Linux-based firmware.

This option is applicable to the DEWE3-M4/ M8s mainframes and all DEWE3-RMx rack-mount mainframe chassis.

Converted to front-ends, these chassis then connect to a separate host PC via LAN interface. OXYGEN software needs to run on the host PC to retrieve, process and store the measurement data from the front-ends.

The standard interface is a 1 GBit Ethernet one. Optionally, a 10 GBit Ethernet interface is available for the DEWE3-RMx systems.





FRONT-ENDS: TRIONet3

- > Up to 100 m distance between the TRIONet3 systems
- > Gigabit LAN and USB3
- > Distributable and stackable



	TRIONet3		
Slots for TRION / TRION3 modules 1)	2 TRION / TRION3		
ow-speed channel expansion	XR modules		
AN	2 x 1000BASE-TX Gigabit Ethernet		
AN configuration	DHCP or Static IP		
JSB	USB 3.0		
Synchronization	TRION-SYNC-BUS up to 100 m between nodes		
System bandwidth	90 MB/s with one connected TRIONet3 (up to 50 MB/s with more than one)		
Display	Status display with touch-screen		
Cooling	2 temperature controlled ultra silent fans		
HOST SYSTEM REQUIREMENTS			
Supported operating systems	Linux or Windows; 64-bit		
Supported interfaces	USB 3.0; 1000BASE-TX Gigabit Ethernet		
POWER SUPPLY			
solated power supply (max.)	10 to 32 V_{DC} (9 to 36 V_{DC})		
Power consumption	Without modules 15 W, totally equipped max. 55 W		
external power supply (included)	100 to 240 V ~50 to 60 Hz / 65 W		
Option	Ext. battery pack, 3 battery slots for ~4 h operation (DW2-UPS-250-DC [see picture above])		
IMENSIONS			
Dimensions (W x D x H)	320 x 205 x 55 mm (12.6 x 8 x 2.2 in.)		
Neight without modules	Typ. 1.9 kg (4.2 lb.)		
NVIRONMENTAL SPECIFICATIONS			
Operating temperature	-20 °C to +60 °C (with pre-warmed unit)		
torage temperature	-20 to +70 °C		
lumidity	10 to 90 % non cond., 5 to 95 % rel. humidity		
1ax. altitude	3000 m (9840 ft)		
ine vibration (EN 60068-2-6)	20 m/s²		
Shock (EN 60028-2-27)	30 g		
Random vibration (EN 60721-3-2)	Class 2M3		





NEX[DAQ] RUGGED & COMPACT

NEX[DAQ] is the flexible "everyday tool" for all test and validation engineers and troubleshooters. Small, lightweight δ very rugged: the 8-channel NEX[DAQ] with universal inputs and a great price performance ratio





IP 67



FANLESS




-20 °C TO +70 °C


		1			
INPUT SIGNALS					
1000	Ι				
VOLTAGE	CURRENT	BRIDGE			
J. E.	₽⊳	\Rightarrow			
LVDT	IEPE/ICP	CHARGE			
		CAN FD			
THERMO.	POTENTIO.	CAN-FD			

005

PUIENTIO.	CAN-FD
P	MSI
Ó	XR
DIGITAL I/O	DEWETRON EXPANSION

	NEX[DAQ]			
Analog input	8 inputs for voltage up to ± 100 V and full/half bridge, TEDS and MSI support			
Further input types, via MSI	IEPE, quarter bridge, charge, RTD, LVDT, thermocouple, 0 to 20 mA, voltage up to $\pm 1000 \text{V}$			
Sampling rate	24-bit, 200 kS/s or 1 MS/s per channel			
Accuracy	± 0.05 % of reading, ± 0.02 % of range $\pm 50~\mu V$			
Hardware filter	Butterworth and Bessel, 2 nd , 4 th , 6 th or 8 th order			
Sensor excitation	1 V to 24 V, freely programmable			
Counters, digital I/O	4 advanced counters and 8 basic counters/digital inputs, 4 digital outputs			
CAN-bus	2 interfaces for CAN2.0 and CAN-FD			
Interface to host PC	USB-C or Ethernet			
Power	9 to 36 V			
Power supply buffer	Buffered for 0.5 s in case of a voltage drop			
Dimensions (W x D x H)	242 x 120 x 43.3 mm (9.52 x 4.72 x 1.7 in.)			
Weight	1.25 kg (2.76 lb.)			
Synchronization	Via Ethernet PTP/IEEE1588			
Topology	Dasychain, Star			

















THERMO-



CAN-BUS



ADAPTER









POTENTIO-



DIGITAL I/O



CHANNEL **EXPANSION**





SPECIFICATION

- > 16 measurement channels expandable via XR modules or MSI sensor interfaces
- > 50 kS/s or 200 kS/s sampling rate
- > Digital I/O and counter
- > CAN (optional)
- > Recording time of 168 h @ 50 kS/s or 42 h @ 200 kS/s
- > Full-HD 15.6" multi-touch display
- > Dimensions (W x D x H) 463 x 129 x 318 mm (18.2 x 5.1 x 12.5 in.)

SOFTWARE

- > Analysis
- > Visualization
- > Post-processing
- > FFT analysis
- > Trigger & events
- > Math & calculation
- > Export features
- > Reporting
- > ...and many more

RECORDING

- > Simple recording and storing of data
- > Quick navigation on your PU[REC] or any PC with our OXYGEN measurement software
- > Effortless data review also while still recording (DejaView)
- > Various trigger conditions and powerful trigger actions
- > Time-based & event-based file-split options
- > Channel-specific storing options for waveform and statistics data recording
- > Easy report and export features

MSI SENSOR ADAPTER

- > MSI (Modular Smart Interfaces) expand the functionality of TRION(3) and PU[REC] inputs
- > Automatically detected and set up
- > Supported on TRION(3)-x-MULTI, TRION(3)-1802 and TRION(3)-1600 with TRION-X-dLV-CB16-D9 connector box



MODULAR SMART INTERFACES (MSI)	INPUT	SENSOR EXCITATION	BANDWIDTH (MAX.)	ACCURACY (TYP.)	SENSOR CONNECTION
MSI2-250R-20mA	4 to 20 mA sensors	5 to 48 V AUX PWR	DC to 250 kHz ¹⁾	±0.1 %	Miniature spring terminals
MSI2-STG	Bridge type sensors Full-bridge, half-bridge, quarter bridge 120 Ω and 350 Ω	5 V and 10 V	60 kHz ¹⁾	±0.1 %	Miniature spring terminals
MSI2-LVDT	LVDT and RVDT sensors, 5- or 6-wire connection	3 V at 2.5, 5 or 18 kHz	1 kHz ¹⁾	±0.1 %	Soldering pads
MSI-BR-ACC	IEPE® sensors, typ. accelerometer, microphone	4 mA	1.4 Hz to 250 kHz ¹⁾	±0.2 %	BNC
MSI2-CH-x	Charge type sensors up to 100 000 pC	n/a	0.08 Hz to 250 kHz ¹⁾	±0.5 %	BNC
MSI2-TH-x	Thermocouple sensors; standard models for type K, J, T (others on request)	n/a	DC to 30 kHz ¹⁾	±1°C	Mini TC socket
MSI-BR-V-200 MSI-BR-V-200 SN: 782285	Voltage up to ±200 V	n/a	DC to 100 kHz ¹⁾	±0.1 %	BNC
MSI2-V-600	Voltage up to 600 V _{RMS}	n/a	DC to 60 kHz ¹⁾	DC to 1 kHz: ±0.1 % of reading ±100 mV >1 kHz to 5 kHz: ±0.5 % of reading ±100 mV >5 kHz to 10 kHz: ±1 % of reading ±100 mV	Safety banana
MSI-BR-RTD MSI-BR-RTD SN. 296285	RTD sensors Pt100, Pt200, Pt500, Pt1000, Pt2000; 2, 3 & 4 wire connection	1.25 mA	DC to 10 kHz ¹⁾	±0.1 %	Binder 712 series 5-pin socket
1) Consider limit of used TRION(3) module					

MSI CONNECTOR BOX

The MSI connector box TRION-X-dLV-CB16-D9 is a feature expansion box for TRION(3)-1802dLV-32 and TRION(3)-1600-dLV-32 modules by MSI (Modular Smart Interfaces) support. This connector box enables measurement of strain gauge and bridge sensors, IEPE®, LVDT and RVDT, thermocouple, charge, RTD and voltage up to $600 \, V_{RMS}$.






Connection to TRION(3)-x-dLV

RUGGED CHANNEL EXPANSIONS

Extend your measurement system with our low-speed channel expansions for temperature, voltage, current or resistance temperature measurements.

- CONTENT OF THE SOUT (SO
- > Ruggedized measurement modules with integrated A/D conversion
- > Extended operating temperature of -40 to +85 °C
- > Fully isolated: channel to channel and channel to bus, power and chassis
- > XR modules are extremely rugged and waterproof
- > RS-485 or CAN interface (freely selectable with programmable interface)
- > Up to 200 Hz sample rate

XR MODULE		CHANNELS	INPUT RANGES	ISOLATION	SAMPLE RATE PER CHANNEL	IP RATING	
XR-RTD8	00000	"[8 isolated resistance temperature detector (RTD) inputs	Resistance: 0 to 5000 Ω RTD: Pt100, Pt200, Pt500, Pt1000, Pt2000	350 V _{DC}	200 S/s	IP 68 immersion depth 3 m
XR-TH8-S	**************************************		8 isoated thermocouple inputs	Types K, J, T, R, S, N, E, L, C, U, B	1500 V _{AC}	200 S/s	tbd.
XR-LA8	00000	I	8 isolated current inputs	0 to 20 mA; ±20 mA; ±30 mA	350 V _{DC}	200 S/s	tbd.
XR-V8	3 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	V	8 isolated voltage inputs	Physical in. range: ±50 V Software selectable: ±100 mV, ±500 mV, ±1 V, ±2.5 V, ±5 V, ±10 V	350 V _{DC}	200 S/s	IP 68 immersion depth 3 m



ANALOG SIGNAL CONDITIONING

Chassis for isolated signal conditioning amplifiers, suitable for a wide variety of sensors.





	DEWE-30-16 DEWE-30-32				
Slots for DAQP modules	16	32			
Interfaces	RS-232, RS-485, XR				
Conditioned signal output	±5 V (±10 V as	option), buffered			
Output connector standard	D-SU	B-37			
Output optional	BNC				
Power supply	100 to 240 V _{AC}				
Optional power supply	10 to 32 V_{DC}				
Dimensions	438.5 x 253 x 133 438.5 x 253 x 253 mm (17.3 x 10 x 5.2 in.) (17.3 x 10 x 9.6 in.)				
Weight (depending on configuration)	4.5 kg (9.9 lb.) 7 kg (15.4 lb.)				
ENVIRONMENTAL SPECIFICATIONS					
Operating temperature	0 to +60 °C				
Storage temperature	-20 to +70 °C				
Humidity	10 to 90 % non cond., 5 to 95 % rel. humidity				
Vibration	EN 60068-2-6, EN 60721-3-2 Class 2M2				
Shock	EN 60068-2-2				

UNIVERSAL ANALOG MEASUREMENT

UNIVERSAL ANALOG MODULE	FEATURES	BANDWIDTH	ISOLATION	CONNECTOR TYPE
DAQP-STG V 10	Auto sensor balance Internal completion for ½ and ¼ bridge µV amplifier with high bandwidth Continuously variable gain from 0.5 to 10 000	300 kHz	350 V _{DC}	D-SUB

COMBINATION WITH TRION(3)/DEWE3-SYSTEMS

Use the TRION(3)-1802-dLV or TRION(3)-1600-dLV as input modules for the conditioned analog signals.




NO LIMITATIONS WITH SYNCHRONIZED SYSTEMS

If you need more than one DAQ system, even on different locations, we have several networking solutions for you.

OXYGEN-NET

The OXYGEN-NET software option makes it possible to combine multiple devices to one virtual measurement device.

- > Easy-to-use synchronized measurement for hundreds of input channels from 10 S/s to 10 MS/s per channel
- > Works with absolute time synchronization (PTP, IRIG, GPS) as well as with the built-in TRION-SYNC-BUS
- > Remote and local data storage possible for redundancy
- > Setup and control of all nodes from the main device




1000s

EXPANSION FOR MORE CHANNELS

You need more channels for your DEWETRON system?


No problem! Expand your system via front-ends or XR modules, depending on the necessary speed.







SYNCHRONIZATION POSSIBILITIES

Synchronization of multiple systems ensures perfectly synchronized measurements without any time shifts between the systems and therefore guarantees highest data quality. DEWETRON offers various synchronization possibilities to have the ideal solution for every application. Different synchronization sources can be used such as GPS, PTP, IRIG or PPS.









DATA ACQUISITION

Synchronous and continuous acquisition of data from several sources: analog, digital, encoder, counter, CAN, SCPI, Ethernet, video, GPS and many more.


- > Analog data with up to 10 MS/s
- > Digital and encoder data with automatic RPM and angle calculation
- > CAN(-FD) decoding via *.dbc including J1939. Compatible with Vector VN-series
- > Ethernet receiver for external sensors (opt.)
- > Video data from USB or GigE-camera
- > Precision GPS position data via TRION3, GeneSys ADMA or OxTS RT series
- > Plugin to request and decode OBD2 parameters



RECORDING

Store all your acquired data in one data file with a simple touch on the record button. You can achieve data rates of up to 1 GB/s and you never have to worry about loosing any data. Furthermore, review your data during recording with the DejaView function.


- > File-split option for generating a new file after an amount of time or event occurrence
- > Channel-wise sample rate selection
- > Channel-specific storing options for waveform and statistics data recording
- > Adjustable playback speed from 1/1000x to 1000x



ANALYSIS AND POST-PROCESSING

The real work often begins after the live measurement. To complete this workflow, OXYGEN also supports post-processing and analysis of the recorded data.


- > Use many of the math and calculation (also incl. FFT) features to refine your measurement results
- > Create new visualizations and measurement
- Quickly navigate through the data with well-known gestures and intuitive zoom and scrolling mechanisms
- > Export data to complete your workflow
- > And the best: You can do that also on your PC license-free!



REPORTING

Use OXYGEN for your whole measurement workflow. From acquiring data to post-processing and finally reporting the data.


- > Create separate reporting pages (additional to the measurment screens) with typical printing layouts
- > Duplicate a measurement screen or create new pages with a simple click
- > Use all instruments and visualizations also in the reporting pages
- > Separte time-cursor on each page available to report different time snippets in one report
- > Directly print or save to pdf
- > Export your measurement to a video



EXPORT


If you need to use other analysis software for further data processing, we offer data export for the most common applications and formats.

- > Universal formats: CSV and TXT with selectable delimiter and timestamp format
- > Advanced formats: Excel, MATLAB, ASAM MDF4, DIAdem, DSPCon, DynaWorks, IMC Famos 2, HDF5, MTS RPC III, NetCFD, NI TDMS, Universal File Format 58, Wave
- > Select channels and/or time-range of the exported data
- > Optional automatic export at measurement end



MATH AND CALCULATION


- > FORMULA: For arithmetic and more advanced calculations (trigonometric, logical and measurement functions)
- > STATISTIC: Block-wise, Triggered and Overall- statistics to calculate statistic values, e.g. AVG, RMS, MIN and MAX, PP...
- > FILTER High, low, bandpass and bandstop IIR-filter and FIR-filter up to the 10th order
- > DMS-ROSETTE calculation module for 45°, 60°, and 90° setups
- > PSOPHOMETRIC ANALYSIS for railway and telecommunication applications
- > FFT spectra overlap, peak hold and pin extraction
- > INTEGRATION / DERIVATION with optional signal filter



TRIGGER & EVENTS

The powerful trigger and event system makes it easy for you to record data in case of events, create marker, set a digital output or make a snapshot of the actual measured data. Create different events, each consisting of one or more trigger conditions and one or more actions.

- > Many different trigger conditions: signal level (positive/negative edge, window) with optional rearm level, keyboard or time
- > Powerful actions like start/stop of recording, set an alarm with optional digital output, set a marker with pre-defined text or make a snapshot of the actual measured data.



VIDEO INPUT

Cameras are implemented as additional sensors in OXYGEN, so you really get the "complete picture" of your measurement task.

Applications start with very simple video documentation (measurement setup, weather, environment, etc.) with a cheap webcam and extend to really complex tasks with up to 8 cameras, whose individual frames are perfectly synchronized with all other data (e.g. analog, CAN, counters, GPS...).

- > USB webcams
- > Synchronized USB and GigE cams, up to 289 fps
- > High-speed cams, up to 100.000 fps (post sync)




OXYGEN-NET

Many applications require more than one measurement device, sometimes even at different locations.

OXYGEN-NET makes it possible, to sum up all devices to one virtual measurement device. You only need a reliable network connection, and you can simply claim all available nodes and operate it from the main device.

- > Create one big virtual device with several remote nodes (measurement cloud)
- > No complicated settings needed, simply claim and remove nodes with one click
- > Works with absolute time synchronization as well as with TRION-SYNC-BUS
- > Remote and local data storage possible for redundancy



SOUND LEVEL

The sound level plugin provides online determination of the time-dependent sound pressure level, the energy equivalent sound pressure level, freely definable statistical sound pressure levels and many more. This plugin turns your DEWETRON device into the ideal solution for analyzing the acoustical emission of machines, for determining the spatial and statistical sound pressure level distribution in buildings and for long-term noise monitoring.


- > A-, B-, C-, D- and Z-frequency weighting (according to DIN EN 61672-1)
- > Fast, slow and impulse time weighting (according to IEC 651)
- > Reference level for air (20 μ Pa) and water (1 μ Pa)
- > Overall and interval logging
- > Audio replay feature



MODAL TEST

With OXYGEN's Modal Test option you can analyze the frequency characteristics of a mechanical structure to determine resonances, damping characteristics and more.


- > DUT excitement via modal hammer
- > SISO & SIMO tests with moving hammer and moving sensor
- > Calculation of
 - > Complex transfer function
 - > Coherence of several hits
 - > Mode indicator function
- > Various interactive visualization options
- > Data export into *.uff and other formats for post processing



ORDER ANALYSIS

The noise and vibration analysis module for rotating machines turns your OXYGEN into a full order analysis instrument for calculation and visualization of frequency and order spectra vs. speed.

- > Simultaneous frequency and order domain analysis
- > Smart resampling algorithm for accurate and fast results
- > Selectable speed ranges from 60 RPM to 100 000 RPM
- > Order resolution from 0.01 to 1, with up to 90 % overlapping
- > Order extraction for selected orders for use in recorder or XY-instrument
- > Visualization of the resulting matrix in intensity diagrams



POWER ANALYSIS

Turn your DEWETRON measurement device into a fully-featured power analyzer:


- > Analysis of 1–9 phase power systems (1P2W, 2V2A, 3P3W, 3P4W, 2x 3P3W, ...)
- > Several power systems are logically summarized into power groups
- > Gapless cycle-by-cycle calc. no blind spots
- > Unique fundamental frequency detection with delay compensation for highest accuracy and reliability
- > BASIC: vol., curr., RMS, AVG, fundamental δ symmetrical components, active/reactive/ apparent power total δ fundamental, energy
- > ADVANCED: harmonics (IEC 61000-4-7), flicker (IEC 61000-4-15), flicker emission (IEC 61400-21) and mechanical power/efficiency
- > EXPERT: rolling calculation meets FGW-TG3



EFFICIENCY MAPS

The matrix sampler is the solution for visualizing the efficiency of your electric drivetrain at different load steps or running speeds online. Create the calculation module directly in your power group. The efficiency map of the drivetrain will be filled up during the measurement.

- > Possibility to refill single measurement points without overwriting the whole matrix
- > Easy-to-use and intuitive operation
- > Several trigger options to fill the map with data
- > Freely definable matrix size
- > Assignment of any channel to X-, Y- and Z-axes for visualizing any 3-dimensional signal dependencies



BIRD'S EYE

The OXYGEN Bird's Eye plugin is the state-ofthe-art software plugin to visualize the testing environment of your (ADAS) test within the software.

Based on the acquired IMU data, the position and movement of all involved objects are updated online. Using the shape editor, a realistic contour of each involved object (i.e. VUT, GVT) can be created for precise distance calculations between test objects.

- Creation of complex 2-dimensional realistic vehicle shapes incl. automatic and EURO NCAP-conform POI-assignment
- > Online distance calculations between all involved objects
- > Proving ground and test setup visualization from the bird's eye view



SDK FOR PROGRAMMERS

With DEWETRON, you get an open platform to develop your own measurement application or extension. Depending on your requirements, you can choose between two Software Development Kits: OXYGEN-SDK and TRION-SDK.

OXYGEN SDK

With OXYGEN SDK, you are capable to develop your own plugins for the OXYGEN measurement software.

AVAILABLE FEATURES FOR THE PLUGIN

- > Advanced calculations and data processing
- > 3rd party data output
- > Data output
- > Special export formats
- > Read and write data from/to numeric channels
- > Create new channels
- > Create config items for setup save/load and user config
 - > Numeric, text, channel list

This and much more allows you, to extend OXYGEN with additional calculations and data I/O.

AVAILABLE FUNCTIONALITY

- > Custom QML-GUI for Add Channel dialog for easy user setup
- > Custom QML-GUI for data export and special options
- > User configuration elements
 - > Text and number inputs for all kinds of configuration
 - > Combo boxes (drop-down & custom input)
 - > File picker for selecting files
- > Read data from any OXYGEN channel
- > Create new OXYGEN channels and write data into

EXAMPLE PLUGIN FUNCTIONALITIES

- > XR plugin
- > OBD2 plugin
- > Frequency measurement

SPECIAL DATA SINKS


> Ethernet sender

SPECIAL EXPORTER

- > Dynaworks
- > DIAdem

SPECIAL DATA SOURCES

- > SCPI query plugin
- > AK dyno plugin
- > Serial CSV reader
- > Modbus TCP/IP



If OXYGEN does not provide a certain function, create it on your own

Get started and visit https://github.com/DEWETRON/OXYGEN-SDK




TRION SDK

The TRION SDK helps you, to build your own measurement application based on the DEWE3 and TRION/TRION3 hardware platforms. It also supports the use of TRIONet.

We support Windows 10 (64-bit), Ubuntu, and Redhat/CentOS Enterprise Linux.

C/C++ are the natively supported programming languages, additional bindings to Python, C# and Delphi.





LINUX OPERATING SYSTEM

We are the only manufacturer of measurement technology to offer you the advantage of choosing between Windows and Linux.

LINUX DISTRIBUTIONS

OXYGEN also runs without restrictions on the Linux operating system.

Beside Windows, our software now supports the distributions Red Hat and Ubuntu.

Measurement setups and DMD measurement data are fully compatible between the different operating systems. This means that it is no problem to create a setup under Windows and then use it on the Linux measurement system.

Also OXYGEN-NET systems can be built from both Windows and Linux based measurement systems.

The choice is yours.

OXYGEN SCPI VI

Use the OXYGEN SCPI interface to transfer data into LabVIEW™ during data acquisition and recording in OXYGEN. Various channels like analog, math or power group channels are supported. The channel setup and configuration is done in OXYGEN and the data can be stored redundantly in OXYGEN and LabVIEW™.

SCOPE OF SUPPLY

- > OXYGEN's SCPI interface for data transfer and configuration
- > LabVIEW[™] VI including the required SCPI commands
- > Documentation included in LabVIEW™ code
- > Quick start programming example
- > Maximum data transfer rate: 10 kS/s
- > Typical number of channels to be transferred: 100 channels

WHEN TO USE

- > Channels calculated in OXYGEN (such as power groups) shall be transferred into LabVIEW™
- > Integration of DEWETRON data acquisition system into a LabVIEW™ based test bed
- > No LabVIEW™ based hardware configuration required

NOTE:

Requires LabVIEW™ on the data acquisition system or on a separate PC that is connected to the same Ethernet network as the data acquisition system.



LABVIEW™ DRIVER FOR TRION(3)

Use the hardware driver to gather data from the TRION API, which is in direct communication with LabVIEW™ . TRION and TRION3 modules in any chassis are supported. The hardware and channel configuration is done in LabVIEW™.


SCOPE OF SUPPLY

- > User friendly encapsulation of the device functions into VIs
- > Possibility to acquire the measurement data from the TRION boards in LabVIEW™ with just a few VIs
- > Dedicated VIs for channel configuration
- > Documentation included in LabVIEW™ code
- > Quick start programming examples included

FOUR SOLUTIONS TO S YOUR MEASUREMENT

WHEN TO USE

- > For customized software solutions developed in LabVIEW™
- > When TRION hardware shall be used in parallel with 3rd party hardware in LabVIEW™
- > For solutions requiring regulation and automation based on LabVIEW™



Requires LabVIEW™ installed on the data acquisition system (or on the host PC in case TRIONet3 is used)

OXYGEN DATASTREAM VI

Use the OXYGEN DataStream interface to transfer data into LabVIEW™ during data acquisition and recording in OXY-GEN. Various channels like analog, math or power group channels are supported. The channel setup and configuration is done in OXYGEN and the data can be stored redundantly in OXYGEN and LabVIEW™.

SCOPE OF SUPPLY

- > OXYGEN's SCPI interface for data transfer and configuration
- > LabVIEW $^{\overline{\text{M}}}$ VI including the required SCPI commands
- > Documentation included in LabVIEW™ code
- > Quick start programming example
- > Maximum data transfer rate: native channel sample rate
- > Typical number of channels to be transferred: 100 channels à 100 kS/s

WHEN TO USE

- > Channels calculated in OXYGEN (such as power groups) shall be transferred into LabVIEW™
- > Integration of DEWETRON data acquisition system into a LabVIEW[™] based test bed
- > No LabVIEW[™] based hardware configuration



EAMLESSLY INTEGRATE 「DATA INTO LABVIEW™

Requires LabVIEW™ on the data acquisition system or on a separate PC that is connected to the same ethernet network as the data acquisiton system

OXYGEN *.TDMS-EXPORT


Export your OXYGEN *.dmd data files directly into the *.tdms format to open the files in LabVIEW™ . Different export options are available (export all or only specific channels, entire data or only specific time span, ...).

SCOPE OF SUPPLY

> Standard OXYGEN *.tdms export


WHEN TO USE

- > Direct export into the LabVIEW™ format
- > Easy integration of data into LabVIEW™
- > No configuration required



CUSTOMER CARE CENTER

Choosing DEWETRON means choosing a partner that accompanies you along the entire way. With the purchase of your DEWETRON system, you benefit immediately from the instant access to our global network of professional support, service and various training offers.



CONTACT OUR SUPPORT TEAM



support@dewetron.com

***** +43 316 3070-555

SEND IN YOUR SYSTEM



For calibration, maintenance and repair issues fill out this form cc.dewetron.com/rma

FOLLOW US ON LinkedIn





Follow us on <u>LinkedIn</u> and you will never miss any DEWETRON update.








CALIBRATION SERVICES


The accuracy of your DEWETRON data acquisition system is paramount. Thus, all DEWETRON systems are of course calibrated before delivery. By calibrating your DAQ system annually, you can ensure the continued integrity of your measurement data.


DEWETRON offers two types of calibration:

- > Standard factory calibration
- > Accredited calibration according to ISO 17025



ACCREDITED SCOPE





POWER CALIBRATION

DC

Especially for your power (analyzer) measurement we offer:

POWER (DC)

- > Calibration of power values (voltage and current applied simultaneously)
- > From power-factor 1 down to 0.1
- > Up to 850 Hz fundamental frequency



TEMPERATURE

WARRANTY **EXTENSION UP TO 5 YEARS**

Generally, all DEWETRON hardware components are covered by a limited one-year warranty covering parts and labor on a depot basis. This standard warranty may be extended to include up to four additional years of assurance.

The premise for the warranty extension up to 5 years*) is the annual calibration and maintenance of your DAQ system by the professionals at the DEWETRON factory.

*) Please check out our terms and conditions for further details.

OUR WARRANTY EXTENSION COVERS FOLLOWING PARTS PC hardware (SSD, mainboard) Power supply DAQ components TRION modules MODULES Sub-modules XR modules








ELECTRICAL POWER & NVH

IN COOPERATION WITH MÜLLER-BBM VibroAkustik Systeme

- > Optimization of NVH (Noise, Vibration and Harshness) & e-power performance through motor control during testing
- > Target-based development of active components on the test bench
- > Correlation analysis between NVH & e-power data for an all-encompassing engineering approach
- > Combination of NVH & e-power data from several sources in only one view
- > Overall e-NVH system analysis with PTP synchronized measurement data



YOUR ADVANTAGES

- > Online data analysis with the processing of NVH ∆ e-power signals in PAK
- > Seamless integration of DEWETRON's power analyzer into the PAK family
- > Optimization of NVH & e-power performance through motor control on test benches
- > Usage of the proven MBBM-VAS rotating machinery software packages
- > Online simulation of vehicle response on test benches using blocked force methodology
- > PTP synchronized data acquisition
- > 10 MS/s & continuous raw data storage for PWM signals with DEWETRON's OXYGEN

DEWETRON + OXYGEN

- > Dedicated power analysis of systems with up to 9 phases with various power parameters
- > Highest flexibility due to a modular design & DEWETRON's mixed signal inputs approach
- > Perfect signal synchronization to guarantee the most reliable measurement data integrity
- Highly dynamic range with tremendous accuracy as a key requirement for test bench applications
- > Continuous & gapless storage of raw data
- > Integrated (redundant) sensor supply for a direct connection to the power analyzer

MBBM-VAS + PAK

- > Open architecture combining data streams from different sources by a live IO hub
- > Direct visualization of acquired quantities & spectral evaluations in the powerful reporting tool (highly interactive graphic functionalities)
- > The perfect solution for troubleshooting, highly standardized tasks, quality assurance, mobile measurements δ test bench operation

ACCESSORIES





CURRENT TRANSDUCERS

We provide several solutions for current measurement: from simple shunts to current clamps and high-precision zero flux transducers. All transducers can be supplied from the DEWETRON instrument.



CURRENT TRANSDUCER SUPPLY

We offer a current transducer box to power up to 8 current transducers directly from your DEWETRON DAQ system




POWER SUPPLY

TRANSPORTATION

We offer special sturdy carrying cases for the safe transport of all our measurement systems.

VIDEO CAMERAS



HIGH SPEED CAMERAS UP TO 100,000 FPS

- > Independent from HS camera system
- > Can be added to every DEWETRON system
- > Measurement screen can be exported as video report
- > Analysis can be done on every computer

USB / ETHERNET CAMERAS UP TO 289 FPS

Rugged and lightweight ALVIUM industrial cameras with high image quality with up to 289 fps. Several models with different resolution and USB 3.0 or GigE connection.







ABOUT DEWETRON

DEWETRON is a manufacturer of precision test ¼ measurement systems designed to help our customers make the world more predictable, efficient and safe. Our strengths lie in customized solutions that are immediately ready for use while also being quickly adaptable to the changing needs of the test environment and sophisticated technology of the energy, automotive, transportation and aerospace industries.

More than 30 years of experience and innovation have awarded DEWETRON the trust and respect of the global market. There are more than 25,000 DEWETRON measurement systems and over 400,000 measurement channels in use in wellknown companies worldwide.

DEWETRON employs over 120 people in 25 countries and is part of the TKH Group, a global corporation, that specializes in the development and supply of innovative solutions worldwide.

DEWETRON's quality is certified in compliance with ISO9001 and ISO14001. The high integrity of the measurement data is guaranteed by our own accredited calibration lab according to ISO17025.

Get to know our **GLOBAL OFFICES**





THE MEASURABLE DIFFERENCE.



DEWETRON

HEADQUARTERS

DEWETRON GmbH Parkring 4, 8074 Grambach **AUSTRIA**

> +43 (0) 316 3070-0 info@dewetron.com www.dewetron.com









